



Product designation Power distribution block

#### Electrical features

Number of poles	2
Rated insulation voltage $U_i$	V 500
IEC Conventional free air thermal current $I_{th}$	A 100
Rated peak withstand current $I_{pk}$	kA 20
Rated short time current $I_{cw}$ 60s	A 4.5

#### Connections

Terminal hole diameter_Option 1	mm	1x8,5mm
Conductor section connectable_Option 1	mm <sup>2</sup>	10...25
Terminal hole diameter_Option 2	mm	3x5,5mm
Conductor section connectable_Option 2	mm <sup>2</sup>	2,5...6
Terminal hole diameter_Option 3	mm	3x4,5mm
Conductor section connectable_Option 3	mm <sup>2</sup>	1,5...4


#### Mechanical features

Operating position	normal allowable	Vertical plane Any
Fixing		Screw / DIN rail 35mm
Phillips		2
Weight	g	130

#### Resistance & Protection

Terminals IP degree	IP20 front
---------------------	------------

#### Dimensions



#### Certifications and compliance

##### Certifications

IEC/EN/BS 60947-7-1

##### Compliance

TÜV

ETIM classification

EC000066 - Power contactor, AC switching

□