



Product designation

Product type designation

Type

Automatic battery
chargers
BCF
Single phase
automatic battery
charger 1
charging level for
lead-acid
batteries

Power supply

Rated voltage U_s

min	VAC	100
Max	VAC	240 $\pm 10\%$

Operational frequency

min	Hz	50 $\pm 5\%$
max	Hz	60 $\pm 5\%$

Power consumption

Max	VA	150
Max	W	70

Power dissipation Max

W	9
---	---

Internal fuse

A	2
---	---

Charging cycle

Reference standards

IEC62368-1

Battery type

lead-acid

Battery voltage

VDC 12

Charging voltage (U_c)

13.6 VDC

Charging current (I_c)

A 4.5

Charging current adjustment

% I_c Fixed

Protections

Main supply fuse;
charging
inhibition due to:
1. Short circuit at
battery terminals;
2. Reverse
battery polarity; 3.
Low voltage at
battery poles; 4.
Output overload.

Indications

LED reverse battery polarity

Yes

Alarm output circuit

Output type

1 relay

Rated capacity

AC1: 3A 250VAC

Mechanical features

Housing type


Modular DIN rail
mounting

Terminals type


Fixed

Fixing				35mm DIN rail or Screw fixing
Weight	g			332
Ambient conditions				
Temperature	Operating temperature			
		min	°C	-40
		max	°C	+51
	Storage temperature			
		min	°C	-40
		max	°C	+85
Protection degree				IP20

Dimensions



Wiring diagrams



Certifications and compliance

Compliance	IEC/EN/BS 60100-6-2
	IEC/EN/BS 61000-6-3
	IEC/EN/BS 62368-1
Certificates	cURus
	EAC

ETIM classification

ETIM 8.0	EC000359 - Universal charger
----------	------------------------------