



Product designation Auxiliary contact
Product type designation BFX12

Contact characteristics

Number of poles	Nr.	2
Rated insulation voltage U_i IEC/EN	V	690
Rated impulse withstand voltage U_{imp}	kV	6
IEC Conventional free air thermal current I_{th}	A	10
Tightening torque for terminals	min Nm	0.8
	max Nm	1
	min lbin	7
	max lbin	9
Max number of wires simultaneously connectable	Nr.	2

Conductor section

AWG/Kcmil

max 14

Flexible w/o lug conductor section

min mm^2 0.75
max mm^2 2.5

Flexible c/w lug conductor section

min mm^2 0.75
max mm^2 2.5

Flexible with insulated spade lug conductor section

min mm^2 0.75
max mm^2 2.5

Mechanical features

Operating position

normal On vertical plane
allowable Any

Fixing Side mounting

Weight g 44

Terminals screw Screw

Conductor section

AWG/kcmil conductor section

max 14

IEC

max mm^2 1 or 2 x 2.5

Auxiliary contact characteristics

Type of contact 1NO+1NC

Thermal current I_{th} A 10

IEC/EN 60947-5-1 designation A600 - Q600

Operating current AC15

230V A 3
400V A 1.9
500V A 1.4

Operating current DC13

24V	A	3
48V	A	1.5
60V	A	1.2
110V	A	0.6
125V	A	0.55
220V	A	0.27
600V	A	0.1

Electrical characteristics

Conductivity	5V 10 mA
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600

Operating current AC15

120V	A	6
240V	A	3
480V	A	1.5
600V	A	1.2

Operating current DC13

12V	A	10
250V	A	0.27
440V	A	0.15
500V	A	0.13

AC coil operating

AC operating voltage

of 50/60Hz coil powered at 50Hz
pick-up

min	%Us	"
max	%Us	"

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	+70


Storage temperature

min	°C	-60
max	°C	+80


Max altitude

m	3000
---	------

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1
CSA C22.2 n° 60947-5-1
IEC/EN 60947-1
IEC/EN 60947-5-1
UL 60947-1
UL 60947-5-1

Certificates

CCC
cULus
EAC

ETIM classification

ETIM 8.0

EC000041 -
Auxiliary contact
block