





Product designation			MODULAR CONTACTOR		
Product type designation			CN		
Operating voltage type			AC/DC		
Number of poles			4		
Number of DIN modules			2		
Electrical features					
IEC Conventional free air thermal current I _{th}			A	25	
Operational current AC1 and AC-7a ≤400V			A	25	
Operational current AC-3 and AC-7b ≤400V			A	8.5	
Rated insulation voltage U _i IEC/EN			V	440	
Rated impulse withstand voltage U _{imp}			kV	4	
Minimum switching capacity			≥17V ≥50mA		
Power dissipation per pole (average value) I _{th}			W	2	
Control circuit					
Auxiliary rated supply voltage U _s			220VAC/VDC		
Auxiliary contacts			NO	Nr. 4	
Average coil consumption ≤20°C			in-rush	W 3	
			holding	W 3	
Operating voltage					
pick-up		min	%U _s	85	
		max	%U _s	110	
	drop-out		min	%U _s	20
			max	%U _s	75
Operating times					
Average time					
Closing NO		min	ms	15	
		max	ms	45	
	Opening NO		min	ms	20
			max	ms	70
Operations					
Mechanical life			cycles	3000000	
Electrical life AC-3			cycles	500000	
Electrical life AC1			cycles	200000	
Ambient conditions					
Operating temperature			min	°C -25	
			max	°C +70	
Storage temperature					

	min	°C	-30
	max	°C	80
Max altitude		m	2000
Mechanical features			
Fixing			DIN rail 35mm
Tightening torque for coil terminal			
	max	Nm	0.6
	max	lbin	0.6
Tightening torque for terminals			
	max	Nm	1.2
	max	lbin	0.9
Conductor section			
Coil terminal			
	min	mm ²	1
	max	mm ²	2.5
Power terminal			
	min	mm ²	1
	max	mm ²	10
Terminals tool			PZ2
Weight		g	260
Resistance & Protection			
Frontal IP degree			IP20
Pollution degree			3
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
IEC/EN 60947-5-1
IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching