



Product designation

Product type designation

Contact elements
- without
mounting adapter
LPXC

Electrical characteristics

Rated insulation voltage Ui IEC/EN	V	690
IEC Conventional free air thermal current Ith	A	10
Conductivity		1mA 5V
UL/CSA and IEC/EN 60947-5-1 designation		A600 Q600
Operating current AC15		

12V	A	6
24V	A	6
48V	A	6
120V	A	6
240V	A	3
400V	A	1.9
480V	A	1.5
500V	A	1.4
600V	A	1.2

Operating current DC13

12V	A	3
24V	A	3
48V	A	1.5
125V	A	0.55
250V	A	0.27
440V	A	0.15
500V	A	0.13
600V	A	0.1

Contact resistance	mΩ	≤20
--------------------	----	-----

Operations

Electrical life	cycles	600000
-----------------	--------	--------

Mechanical features

Operating force	kg-lb	≤0.5Kg/1.1lb
Tightening torque for terminals max	Nm	1
Terminals screw		Screw

Conductor section

AWG/kcmil conductor section

max 14

IEC

max mm² 1 or 2 / 2.5

Mounting adapter		LPXAU120
------------------	--	----------

Weight	g	11
--------	---	----

Ambient conditions


Temperature

Operating temperature

min °C -25

Storage temperature	max	°C	+70
	min	°C	-40
	max	°C	+85

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

CCC
cULus
EAC
RINA

ETIM classification

ETIM 8.0

EC000041 -
Auxiliary contact
block