



Product designation

INDUSTRIAL
RELAYS
HR602C

Product type designation

Contact characteristics

Contact configuration	2 C/O		
Rated insulation voltage U_i IEC/EN	V	500	
Rated impulse withstand voltage U_{imp}	kV	4	
IEC Conventional free air thermal current I_{th}	A	7	
Rated current (I_n)	A	7	
Relay control voltage	V	230VAC	
Max contrallable power in	AC-1	W	7
Rated operating power AC-1		VA	1750
Rated operating power AC-15	230 VAC	VA	150
Single-phase motor control	230VAC	kW	0.37
Rated operating current DC-1	30V	A	12
	110V	A	0.3
	220V	A	0.1

Minimum switching load	V / mA	5 / 100
Contact impedance	mΩ	100
Contact material	Ag/Ni	

Operating times

Closing	ms	<25	
Opening	ms	<25	

Operations

Mechanical life	cycles	20000000	
Electrical life AC1	cycles	100000	

Coil characteristics

Average coil consumption AC at 20°C	VA	1.7	
Average coil consumption DC at 20°C	W	1.1	

Operating range

Closing	% U_n	70...110
Opening	% U_n	20...55

Maximum cycle frequency	cycles/h	3600	
-------------------------	----------	------	--

Mechanical features

Max socket terminal tightening torque	Nm	0.6
Socket screw tightening tool (cross / flat blade)	PH1 / 4.5mm	
Conductor section		

Conductor section

AWG/Kcmil

min	20
max	14

IEC

min	mm ²	0.5
max	mm ²	2.5

Operating position

normal	Any
--------	-----

Fixing

On 35mm DIN
rail and with
screw

Ambient conditions

Temperature

Operating temperature

min	°C	-40
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+80

Other features

Indication

Yes

Mechanical contact position indicator


Yes

Mechanical test actuator


Yes

Dimensions


HR60 2C... with socket HR6XS21 - HR6XS22





HR60 4C... with socket HR6XS41 - HR6XS42



HR60 2C... - HR60 4C... with socket HR6XS21S - HR6XS41S



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

CSA

cURus

EAC

VDE

ETIM classification

ETIM 8.0

EC001437 -
Switching relay