




Product designation			Direct-on-line starter
Product type designation			M1P01812...B1
Electrical features			
Relay adj range	A	13-18	
IEC technical characteristics (≤440V)		Ie kW	A kW 18 7.5
Components			
Starter enclosure standard supplied		M1PA	
Contactor standard supplied		BF1810A	
Thermal relay standard supplied		RF381800	
UL technical data			
Maximum UL/CSA horsepower ratings single-phase		110V-120V 220V-240V	HP HP 1 3
Maximum UL/CSA horsepower ratings three-phase, 3-pole		200V-208V 220V-240V 440V-480V 550V-600V	HP HP HP HP 5 5 10 15
Mechanical features			
Weight		g	1040
Ambient conditions			
Operating temperature		min max	°C °C -25 +60
Storage temperature		min max	°C °C -40 +70
Resistance & Protection			
Frontal IP degree		IP65	
Dimensions			





I = Start; O = Stop/Reset

Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508 CSA C22.2 n° 14

Certificates

CSAus

cULys

EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination