



Electric fire pump controller, supply 24VAC, built-in RS485, not expandable FFL...EP

Product designation

Product type designation

Auxiliary supply

| | |
|---------------------------------------|----------------|
| Rated auxil. supply voltage | 24VAC |
| Operating auxil. supply voltage range | 19.2...28.8VAC |
| Operating frequency range | Hz 45...66Hz |

Voltage inputs

| | | |
|---------------------|-------------|-------------|
| Rated voltage U_s | min VAC 100 | Max VAC 600 |
| Measurement range | V | 100...720 |
| Frequency range | Hz | 45...66 |

NTC probe input

| | |
|---------------------------|-------------------------|
| Sensor type | NTC (LOVATO code NTC01) |
| Measuring range | °C -40...+85 |
| Maximum connection length | mt 3m |

Digital inputs

| | |
|----------------------------|-------------------------|
| Number of digital input | Nr. 8 |
| Digital input type | Negative |
| Digital input current | mA ≤6 |
| High digital input signal | V ≥4.9V (typical 3.8V) |
| Low digital input signal | V ≤1.25V (typical 2.3V) |
| Digital input signal delay | ms ≥50 |

Current inputs

| | |
|-------------------------|--------------|
| Rated current (I_e) | A /1A or /5A |
|-------------------------|--------------|

Relay outputs

| | |
|------------------------|-----------------|
| Number of relay output | Nr. 7 |
| Mechanical endurance | 10 ⁷ |
| Electrical endurance | 10 ⁵ |

Static Outputs

| | |
|-------------------------|--------------|
| Number of static output | 1 (OUT10) |
| Static output type | NO |
| Operating voltage | V 10...30VDC |
| Maximum current | mA 50mA |

RS485 serial interface

| | |
|----------------------------------|---------------------------------|
| Interface type | Isolated RS485 serial interface |
| Baud rate | bps 1200...115200 |
| Insulation voltage (RS485-Vbatt) | 1kVDC |

Connections

| | | | |
|---------------------------------|----------------------|-----------------|------|
| Type of terminal | Removable screw-type | | |
| Conductor cross section | | | |
| AWG/Kcmil | min | AWG | 24 |
| | Max | AWG | 12 |
| IEC | min | mm ² | 0.2 |
| | Max | mm ² | 2.5 |
| Tightening torque for terminals | max | Nm | 0.56 |
| | max | lbin | 5 |


Ambient conditions

| | | | |
|-----------------------|-----|----|----------------------------|
| Temperature | | | |
| Operating temperature | min | °C | -25 |
| | max | °C | +70 |
| Storage temperature | min | °C | -30 |
| | max | °C | +80 |
| Relative humidity | | | % <80% (IEC/EN 60068-2-78) |


Housing

| | | | |
|------------------------|------------------------------------|------------------|--|
| Execution | Flush-mount | | |
| Material | Polycarbonate | | |
| Degree of protection | IP65 Frontal; IP20 on terminals | | |
| Dimensions (W x H x D) | mm | 240 x 180 x 43.9 | |
| Weight | g | 980 | |

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61000-6-2

IEC/EN 61000-6-3

IEC/EN 61010-1

IEC/EN 61010-2-030

UNI EN 12845

Certificates

/

ETIM classification

ETIM 8.0

EC002685 -
Central fire alarm
control panel