



Level control
relay for
emptying
function. Single
voltage. Modular
version - KIT
LVMKIT20
Emptying

Product designation

Product type designation

Function

Auxiliary supply

Supply voltage Type	Single voltage
---------------------	----------------

Rated auxiliary supply voltage U_s	
AC	

	min	VAC	24
Operating voltage range			0.85...1.1 U_s
Rated frequency		Hz	50/60
Power consumption Max		VA	3.5
Power dissipation Max		W	1.8

Output characteristics

Number of connectable electrodes	Nr.	3
----------------------------------	-----	---

Type of electrode

		Electrode and electrode holders: SN1 / SCM / CGL / PS31 / PS3S or similar
--	--	------------------------------------------------------------------------------------------

Electrode voltage		7.5 VAC
-------------------	--	---------

Sensitivity	k Ω	2.5...50 adjustable
-------------	------------	------------------------

Time delay

Tripping time	s	≤ 0.6
---------------	---	------------

Resetting time	s	≤ 0.75
----------------	---	-------------

Relay outputs

Number of relays	Nr.	1
------------------	-----	---

Relay state

		Normally de- energised, energises at tripping
--	--	--------------------------------------------------------

Contact arrangement

		1 changeover contact C/O- SPDT
--	--	--------------------------------------

Rated operational voltage AC (IEC)	VAC	250
------------------------------------	-----	-----

Maximum switching voltage	VAC	400
---------------------------	-----	-----

IEC Conventional free air thermal current I_{th}	A	8
----------------------------------------------------	---	---

UL/CSA and IEC/EN 60947-5-1 designation		B300
-----------------------------------------	--	------

Electrical life (with rated load)	cycles	10^5
-----------------------------------	--------	--------


Mechanical life	cycles	30×10^6
-----------------	--------	------------------

Indications


Indication				1 green LED for power on 1 red LED for relay state
Functions				
3 detecting electrodes (MIN, MAX and COM)				Yes
5 detecting electrodes (MIN1, MAX1, MIN2, MAX2 and COM)				No
Sensitivity adjustment 2.5...50k Ω				Yes
Sensitivity adjustment 2.5...100k Ω				No
Sensitivity adjustment 2.5...200k Ω				No
Adjustable sensitivity full-scale value 25-50-100-200 k Ω				No
Separate sensitivity adjustment for MAX probe (foam detection)				No
Emptying function				Yes
Filling function				No
Emptying function with MIN and/or MAX alarm				No
Filling function with MIN and/or MAX alarm				No
Emptying function with pump priority change				No
Filling function with pump priority change				No
Tank filling, well drawing and alarm				No
Filling-emptying adjustment selector				No
Programming selector for 5 different				No
Motor start-up priority change				No
Connections				
Terminals type				Screw
Tightening torque for terminals	max	Nm	0.8	
	max	lbin	7	
Conductor cross section				
AWG/Kcmil	min	AWG	24	
	Max	AWG	12	
IEC	min	mm²	0.2	
	Max	mm²	4	
Insulations				
Rated insulation voltage Ui			V	415
Rated impulse withstand voltage Uimp			kV	6
Operating frequency withstand voltage			kV	4
Double insulation Supply / relay / electrode			VAC	≤250
Ambient conditions				
Temperature				
Operating temperature	min	°C	-20	
	max	°C	+60	
Storage temperature	min	°C	-30	
	max	°C	+80	
Housing				
Execution				Modular DIN rail mounting
N° of modules				2
Material				Self-extinguishing polyamide

Mounting	35mm DIN rail (IEC/EN 60715) or by screws using extractable clips	
IEC degree of protection	IP40 on front / IP20 on terminals	
Dimensions (W x H x D)	mm	35.8 x 104.7 x 64.9
Weight	g	215

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN 60255-5
IEC/EN 61000-6-2
IEC/EN 61000-6-3
UL508

Certificates

/

ETIM classification

ETIM 8.0

EC001447 - (Fill)
level monitoring
relay