



Product designation			MODULAR CONTACTOR	
Product type designation			CNM	
Operating voltage type			AC/DC	
Manual control			YES	
Number of poles			2	
Number of DIN modules			1	
Electrical features				
IEC Conventional free air thermal current I _{th}			A	20
Operational current AC1 and AC-7a ≤400V			A	20
Operational current AC-3 and AC-7b ≤400V			A	9
Rated insulation voltage U _i IEC/EN			V	440
Rated impulse withstand voltage U _{imp}			kV	4
Minimum switching capacity			≥17V ≥50mA	
Power dissipation per pole (average value) I _{th}			W	1.7
Control circuit				
Auxiliary rated supply voltage U _s			220VAC/VDC	
Auxiliary contacts			NO	Nr. 2
Average coil consumption ≤20°C			in-rush	W 2.5
			holding	W 2.5
Operating voltage				
pick-up			min	%U _s 85
			max	%U _s 110
	drop-out		min	%U _s 20
			max	%U _s 75
Operating times				
Average time				
Closing NO			min	ms 15
			max	ms 45
	Opening NO		min	ms 25
			max	ms 50
Operations				
Mechanical life			cycles	3000000
Electrical life AC-3			cycles	300000
Electrical life AC1			cycles	200000
Ambient conditions				
Operating temperature			min	°C -25
			max	°C +70

Storage temperature

min	°C	-30
max	°C	80

Max altitude

m	2000
---	------

Mechanical features

Fixing

DIN rail 35mm

Tightening torque for coil terminal

max	Nm	0.6
max	lbin	0.6

Tightening torque for terminals

max	Nm	1.2
max	lbin	0.9

Conductor section

Coil terminal

min	mm ²	1
max	mm ²	2.5

Power terminal

min	mm ²	1
max	mm ²	10

Terminals tool

PZ2

Weight

g 135

Resistance & Protection


Frontal IP degree

IP20


Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching