

3 PHASE VOLTAGE VALUES, 3 PHASE TO PHASE VOLTAGE VALUES, 3 MAX PHASE VOLTAGE VALUES, 3 MAX PHASE TO PHASE VOLTAGE VALUES, 3 MIN PHASE VOLTAGE VALUES, 3 MIN PHASE TO PHASE VOLTAGE VALUES. RELAY OUTPUT CU CONTROL AND PROTECTION FUNCTIONS



Metering instruments -
Voltmeter
DMK70R1
3

Product designation

Product type designation

DIN rail module number

Auxiliary supply Us

Auxiliary rated supply voltage AC	VAC	220...240
-----------------------------------	-----	-----------

Operational frequency

min	Hz	50
max	Hz	60

Power consumption

Max	VA	3.6
-----	----	-----

Power dissipation Max

W	1.8
---	-----

Measuring voltage inputs

Rated voltage (Ue)

phase-phase	VAC	600
phase-neutral	VAC	347

Operating voltage range

phase-phase	VAC	15...660
phase-neutral	VAC	10...382

Voltage inputs operational frequency

min	Hz	45
max	Hz	66

Voltage inputs measurement method

True RMS

Accuracy

VLN voltage	±0.25% f.s. ±1 digit
VLL voltage	±0.25% f.s. ±1 digit

Insulations

Rated insulation voltage Ui IEC/EN

V	600
---	-----

Mechanical features

Housing type

Polyamide

Terminals type

Fixed

Conductor cross section

min	mm ²	0.2
Max	mm ²	4
min	AWG	24
Max	AWG	12

Tightening torque (Max)

Nm	0.5
lbin	4.5

Fixing

Din rail

Weight

g	264
---	-----

Ambient conditions

Temperature

3 PHASE VOLTAGE VALUES, 3 PHASE TO PHASE VOLTAGE VALUES, 3 MAX PHASE VOLTAGE VALUES, 3 MAX PHASE TO PHASE VOLTAGE VALUES, 3 MIN PHASE VOLTAGE VALUES, 3 MIN PHASE TO PHASE VOLTAGE VALUES. RELAY OUTPUT CU CONTROL AND PROTECTION FUNITIONS

Operating temperature

min	°C	-20
max	°C	+60


Storage temperature

min	°C	-30
max	°C	+80


Protection degree

IP40

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61000-6-2

IEC/EN 61000-6-3

IEC/EN 61010-1

Certificates

EAC

ETIM classification

ETIM 8.0

EC002306 -
Voltmeter for
installation