



Product designation

Direct-on-line
starter

Product type designation

M0P00912...5

Electrical features

Relay adj range	A	3-5
IEC technical characteristics ($\leq 440V$)	<div> <div>le</div> <div>kW</div> </div>	<div> <div>A</div> <div>kW</div> </div> <div> <div>5</div> <div>1.5...2.2</div> </div>

Components

Starter enclosure standard supplied	M0PA
Contactor standard supplied	BG0910A
Thermal relay standard supplied	RF95

UL technical data

Maximum UL/CSA horsepower ratings single-phase	220V-240V	HP	0.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	1
	220V-240V	HP	1
	440V-480V	HP	3
	550V-600V	HP	3

Mechanical features

Weight	g	760
--------	---	-----


Ambient conditions

Operating temperature	<div>min</div> <div>max</div>	<div>°C</div> <div>°C</div>	<div>-25</div> <div>+60</div>
Storage temperature	<div>min</div> <div>max</div>	<div>°C</div> <div>°C</div>	<div>-40</div> <div>+70</div>


Resistance & Protection

Frontal IP degree	IP65
-------------------	------

Dimensions



Wiring diagrams



I = Start; O = Stop/Reset

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
UL508 CSA C22.2 n° 14

Certificates

CSAus
cULus
EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination