



Product designation

Direct-on-line
starter

Product type designation

M0R00912...2V3

Electrical features

Relay adj range	A	1.4-2.3
IEC technical characteristics ($\leq 440V$)		
	I _e kW	A kW
	2.3	0.55...0.75

Components

Starter enclosure standard supplied	M0RA
Contactor standard supplied	BG0910A
Thermal relay standard supplied	RF92V3

Mechanical features

Weight	g	720
--------	---	-----


Ambient conditions

Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70


Resistance & Protection

Frontal IP degree	IP65
-------------------	------

Dimensions



Wiring diagrams



R = Reset; I = Start; O = Stop

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
UL508 CSA C22.2 n° 14

Certificates

CSAus
cULus
EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination