



Product designation

Product type designation

Auxiliary supply voltage

Number of inputs

Number of outputs

Max I/O number

Training kit with
LRD12RD024
mounted on
input/output
simulation board
LRDDEM12RD024
24VDC
Nr. 6 digital + 2
digital/analog
Nr. 4 relay
12 (8 inputs + 4
outputs) up to 36
with LRE
modules

Power supply

Operating voltage range		20.4...28.8VDC
Average current consumption	mA	125
Power consumption Max	W	4.5

Digital inputs

Number of digital input	Nr.	6 + 2 digital/analog
Rated voltage	V	24VDC
Input signals	State 0 (OFF) State 1 (ON)	<5VDC >15VDC
Response time	0 to 1 (OFF-ON) 1 to 0 (ON-OFF)	4ms (0.5ms for high speed) 4ms (0.3ms for high speed)

Analog inputs

Number of analog input	Nr.	2 digital/analog
Analog input type		Voltage inputs
Inputs signal range	V	0...10
Resolution		0.01V
Bit of conversion	bit	10
Current consumption at	10VDC	mA <0.17mA
Input impedance	kΩ	>40
Admissible overload	VDC	28
Sampling time	ms	5...20ms(LADDER, 2...10ms (FBD)
Maximum cable lenght	m / ft	≤30m/98ft (shielded wire)

Digital outputs

Number of digital output	Nr.	4
type		Relay

System resources

Display	LCD display, 4 lines x 16 characters
---------	--------------------------------------

Connections

Terminals type	Screw
Tightening torque for terminals	max Nm 0.6 Max lbft 0.4
Conductor section	
AWG/Kcmil	min 26 max 14
IEC	min mm ² 0.14 max mm ² 2.5

Ambient conditions

Temperature			
Operating temperature	min °C -20 max °C +55		
Storage temperature	min °C -40 max °C +70		
Relative humidity	%	20...90% without condensation	

Housing

Mounting	35mm DIN rail or screw fixing (M4x20mm)
Degree of protection	IP20
Weight	g 920

Certifications and compliance

Compliance	CSA C22.2 n° 142 IEC/EN 61131-2 UL508
Certificates	cULus EAC

ETIM classification

ETIM 8.0	EC002581 - PLC device set
----------	---------------------------