



Product designation

Direct-on-line  
starter

Product type designation

M0P00912...75

#### Electrical features

Relay adj range	A	4.5-7.5
IEC technical characteristics ( $\leq 440V$ )		
	I <sub>e</sub> kW	A kW
		7.5 2.2...3

#### Components

Starter enclosure standard supplied	M0PA
Contactor standard supplied	BG0910A
Thermal relay standard supplied	RF975

#### UL technical data

Maximum UL/CSA horsepower ratings single-phase	220V-240V	HP	0.75
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	1.5
	220V-240V	HP	2
	440V-480V	HP	5
	550V-600V	HP	5

#### Mechanical features

Weight	g	760
--------	---	-----

#### Ambient conditions


Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70

#### Resistance & Protection


Frontal IP degree	IP65
-------------------	------

#### Dimensions

DIRECT-ON-LINE-STARTER, 4.5...7.5A (2.2...3KW AT 400V), IP65, CONTACTOR COIL  
VOLTAGE 400VAC 50/60HZ, NON-METALLIC ENCLOSURE, WITH THERMAL OVERLOAD  
RELAY, WITH START AND STOP/RESET BUTTONS



## Wiring diagrams



I = Start; O = Stop/Reset

## Certifications and compliance

## Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508 CSA C22.2 n° 14

## Certificates

CSAus

---

cULys

EAC

## ETIM classification

ETIM 8.0

EC001037 -  
Motor  
starter/Motor  
starter  
combination