



Product designation

Product type designation

Operating voltage type

Application

Number of poles

Number of DIN modules

SPD according to IEC/EN 61643-11

Surge Protection
Device (SPD)

SG2

AC

AC Power lines

2P

1

YES

Electrical features

IEC Maximum continuous voltage U_c	V	320
IEC Maximum discharge current I_{max} 8/20 (L-N/N-PE)	kA	15
IEC Rated discharge current (IEC) I_n 8/20 (L-N/N-PE)	kA	5
IEC Voltage protection level U_p (L-N/N-PE)	kV	<1.5
IEC Follow current I_f (N-PE) rms	A	No
Tripping time t_a (L-N/N-PE)	ns	<25
Thermal insulation protection		YES
IEC Backup protection fuse with supply fuse >63A (L-N/N-PE)	Class/A	63A Gg
IEC Maximum short circuit current at 50Hz	kA	6
Status indicator - operating / end of life		Frontal indication

Ambient conditions

Operating temperature

min	°C	-40
max	°C	+85

Max altitude

m 2000

Mechanical features

Fixing

Din rail

Conductor section Flexible max (IEC)

mm² 4 (L,N) / 25 (PE)


Conductor section Rigid max (IEC)

mm² 6 (L,N) / 35 (PE)


Weight

g 144

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61643-11

Certificates

EAC

ETIM classification

ETIM 8.0

EC000941 -
Surge protection
device for power
supply systems