





Product designation			MODULAR CONTACTOR	
Product type designation			CN	
Operating voltage type			AC/DC	
Number of poles			4	
Number of DIN modules			2	
Electrical features				
IEC Conventional free air thermal current I _{th}			A	25
Operational current AC1 and AC-7a ≤400V			A	25
Operational current AC-3 and AC-7b ≤400V			A	8.5
Rated insulation voltage U _i IEC/EN			V	440
Rated impulse withstand voltage U _{imp}			kV	4
Minimum switching capacity			≥17V ≥50mA	
Power dissipation per pole (average value) I _{th}			W	2
Control circuit				
Auxiliary rated supply voltage U _s			24VAC/DC	
Auxiliary contacts			NO	Nr. 4
Average coil consumption ≤20°C			in-rush	W 3
			holding	W 3
Operating voltage				
pick-up			min	%U _s 85
			max	%U _s 110
	drop-out		min	%U _s 20
			max	%U _s 75
Operating times				
Average time				
Closing NO			min	ms 15
			max	ms 45
	Opening NO		min	ms 20
			max	ms 70
Operations				
Mechanical life			cycles	3000000
Electrical life AC-3			cycles	500000
Electrical life AC1			cycles	200000
Ambient conditions				
Operating temperature			min	°C -25
			max	°C +70
Storage temperature				

	min	°C	-30
	max	°C	80
Max altitude		m	2000
Mechanical features			
Fixing			DIN rail 35mm
Tightening torque for coil terminal			
	max	Nm	0.6
	max	lbin	0.6
Tightening torque for terminals			
	max	Nm	1.2
	max	lbin	0.9
Conductor section			
Coil terminal			
	min	mm ²	1
	max	mm ²	2.5
Power terminal			
	min	mm ²	1
	max	mm ²	10
Terminals tool			PZ2
Weight		g	260
Resistance & Protection			
Frontal IP degree			IP20
Pollution degree			3
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching