





Product designation			MODULAR CONTACTOR		
Product type designation			CN		
Operating voltage type			AC/DC		
Number of poles			4		
Number of DIN modules			2		
Electrical features					
IEC Conventional free air thermal current I <sub>th</sub>			A	32	
Operational current AC1 and AC-7a ≤400V			A	32	
Operational current AC-3 and AC-7b ≤400V			A	8.5	
Rated insulation voltage U <sub>i</sub> IEC/EN			V	440	
Rated impulse withstand voltage U <sub>imp</sub>			kV	4	
Minimum switching capacity			≥17V ≥50mA		
Power dissipation per pole (average value) I <sub>th</sub>			W	2.5	
Control circuit					
Auxiliary rated supply voltage U <sub>s</sub>			220VAC/VDC		
Auxiliary contacts			NO	Nr.	4
Average coil consumption ≤20°C			in-rush	W	3
			holding	W	3
Operating voltage					
pick-up	min	%U <sub>s</sub>	85		
	max	%U <sub>s</sub>	110		
drop-out	min	%U <sub>s</sub>	20		
	max	%U <sub>s</sub>	75		
Operating times					
Average time					
Closing NO	min	ms	15		
	max	ms	45		
Opening NO	min	ms	20		
	max	ms	70		
Operations					
Mechanical life			cycles	3000000	
Electrical life AC-3			cycles	500000	
Electrical life AC1			cycles	150000	
Ambient conditions					
Operating temperature			min	°C	-25
			max	°C	+70
Storage temperature					

	min	°C	-30
	max	°C	80
Max altitude		m	2000
<b>Mechanical features</b>			
Fixing			DIN rail 35mm
Tightening torque for coil terminal			
	max	Nm	0.6
	max	lbin	0.6
Tightening torque for terminals			
	max	Nm	1.2
	max	lbin	0.9
Conductor section			
Coil terminal			
	min	mm <sup>2</sup>	1
	max	mm <sup>2</sup>	2.5
Power terminal			
	min	mm <sup>2</sup>	1
	max	mm <sup>2</sup>	10
Terminals tool			PZ2
Weight		g	260
<b>Resistance &amp; Protection</b>			
Frontal IP degree			IP20
Pollution degree			3
<b>Dimensions</b>			



## Wiring diagrams



## Certifications and compliance

### Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC