




Product designation	Three-phase energy meters		
Product type designation	DMED330		
Type	Three-phase with and without neutral		
DIN rail module number	4		
Auxiliary supply U_s			
Operational frequency	min	Hz	50
	max	Hz	60
Power consumption	Max	VA	3.5
Power dissipation Max		W	2.7
Measuring voltage inputs			
Rated voltage (U_e)	phase-phase	VAC	380...415
	phase-neutral	VAC	220...240
Operating voltage range	phase-phase	VAC	323...456
	phase-neutral	VAC	187...264
Connection method	Via CT		
Current			
IEC maximum (I_{max})		A	5
IEC minimum (I_{min})		A	0.05
IEC rated (I_{ref-Ib})		A	5
IEC start (I_{st})		mA	0.005
Transition (I_{tr})		A	0.25
Accuracy			
	Active energy		Class 0.5s (IEC/EN 62053-22)
	Reactive energy		Class 2 (IEC/EN 62053-23)
Output characteristics			
LED Pulse rate		pulse/kWh	1000
LED Pulse duration		ms	30
Insulations			
Rated insulation voltage U_i IEC/EN		V	250
Rated impulse withstand voltage U_{imp}		kV	6
Operating frequency withstand voltage		kV	4
Mechanical features			
Housing type			Polyamide
Terminals type			Fixed
Conductor cross section	min	mm ²	0.2


					4 for supply voltage measurement; 2.5 for current measurement
	Max	mm ²			
	min	AWG			24
	Max	AWG			12
Tightening torque (Max)					
		Nm			0.8
		lbin			7
Fixing					Din rail
Weight		g			332
Ambient conditions					
Temperature					
	Operating temperature				
	min	°C			-25
	max	°C			+55
	Storage temperature				
	min	°C			-25
	max	°C			+70
Relative humidity		%			<80
Maximum Pollution degree					2

Dimensions




Wiring diagrams


Single-phase





Two-phase




Three-phase with or without neutral




Three-phase without neutral in ARON connection



Tariff input




Pulse output 30VDC 50mA for DME D305 T2



RS485 for DME D330



M-Bus for DME D332



Certifications and compliance

Compliance

IEC/EN 50470-1

IEC/EN 61010-1

IEC/EN 61010-2-030

Certificates

EAC

RCM

ETIM classification

ETIM 8.0

EC001506 -
Kilowatt-hour
meter